# AvaSpec-RS Replaceable-Slit Spectrometer

#### **AvaSpec-RS**

For most customers the choice between throughput and resolution is not an easy one. Avantes now offers the possibility for end-users to easily replace a slit through the introduction of our replaceable-slit feature. The replaceable slit option is available on ULS Ultra-low Stray-light AvaSpecs. On our AvaSpec-HERO & NIR spectrometers this is standard. The slit sets contain 25, 50, 100 and 200 µm slits along with a screwdriver tool to

facilitate the change. Slit kits are available with SMA-905 connector, as well as FC/PC connectors. Slit sets can be ordered separately for the -RS spectrometer.

No recalibration of the spectrometer is needed when changing slit because of the high-precision slit positioning.



## **Technical Data**

Slit set connect Slit siz Mater **Fixing scre** 

ors	SMA-905 or FC/PC
zes	25, 50, 100, 200 or 500 μm (width) x 1 mm (height)
rial	Stainless steel
ews	Torx (included)

Specify slit size XX=25, 50, 100, 200 or 500 µm, in combination with AvaSpec-ULS-RS

### **Ordering Information**

-RS • Replaceable slit, to be added to the product code of the AvaSpec-ULS

SLIT-XX-RS

spectrometers **SLIT-XX-RS-FCPC** • as SLIT-XX-RS, but with FC/PC connector

• Replaceable slit with SMA connector.

### Slit Kit

To fully utilize your AvaSpec-RS series spectrometer with replaceable slit, the Slit Kit is available. It features a complete set with four slits, of 25, 50, 100, 200 and 500  $\mu m.$  Also included in the kit are the tools to easily change the slit in the spectrometer.

The Slit Kit is available in SMA (choice of 4 SMA slits), SMA/FCPC (combination of 2 SMA and 2 PCPC slits) and FC/PC (choice of 4 FCPC and/or SMA slits) versions.

All kits can be used on any spectrometer with the replaceable slit option installed. Slit sizes 5 and 10 um cannot be included in the kit, but can be ordered as a separate item (recalibration of spectrometer recommended).



### Ordering Information

• Slit kit containing of 4 SMA replaceable slits. Choice of 25, 50, 100, 200 and 500  $\mu m$  slits (any combination), and the tools to replace the slit

• Slit kit containing of 2 SMA and 2 FCPC replaceable slits.. Choice of 25, 50, 100, 200 and  $500\ \mu m$  slits (any combination), and the tools to replace the slit

SLITKIT-FCPC

SLITKIT-SMA/FCPC

SLITKIT-SMA

• Slit kit containing of 4 replaceable slits (FCPC and/or SMA). Choice of 25, 50, 100, 200 and 500  $\mu m$  slits (any combination), and the tools to replace the slit.

Don't forget to order a fiber cable



www.phototechnica.co.jp フォトテクニカ株式会社

〒336-0017 埼玉県さいたま市南区南浦和 1-2-17 TEL:048-871-0067 FAX:048-871-0068 e-mail:voc@phototechnica.co.jp