



QE65

65 x 65 mm, 10 μ J - 200 J



KEY FEATURES

1. **MODULAR CONCEPT**
Increase the power capability of your detector:
2 different cooling modules
 2. **LARGE APERTURE**
Effective aperture of 65 x 65 mm
 3. **QED ATTENUATOR AVAILABLE**
 - Measure up to 5X higher energies
 - Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength
 4. **LOW NOISE LEVEL**
10 μ J for the MB coating
 5. **TEST TARGET INCLUDED**
With the MB models
 6. **SMART INTERFACE**
Containing all the calibration data
7. **integra OPTIONS**

 - Standard: USB Output (-INT)
 - In Option: RS-232 Output (-IDR) and External Trigger (-INE)

AVAILABLE MODELS



QE65LP-S-MB
(Broadband-Convection)



QE65LP-H-MB
(Broadband-Heatsink)



QE65ELP-S-MB
(XLong Pulse-Convection)



QE65ELP-H-MB
(XLong Pulse-Heatsink)

ACCESSORIES



Stand with Delrin Post
(200428, For -S Model)



Stand with Delrin Post
(201284, For -H Model)



DB-15 to BNC Adaptor
(Model Number: 200036)



QED-65 Attenuator
(Model Number: 201282)



Pelican Carrying Case

SEE ALSO

HOW IT WORKS	12
CALIBRATION	6
TECHNICAL DRAWINGS	62
ABSORPTION CURVES	64
QED ATTENUATOR	41
COMPATIBLE MONITORS	
MAESTRO	20
S-LINK	28
M-LINK	32
LIST OF ALL ACCESSORIES	194
APPLICATION NOTE	
LONG PULSE JOULEMETER	
IN BURST MODE	

QE65



*Also traceable to NRC-CNRC

SPECIFICATIONS

	QE65LP-S-MB		QE65LP-H-MB		QE65ELP-S-MB		QE65ELP-H-MB	
MAX MEASURABLE ENERGY (WITH ATTENUATOR)	200 J		200 J		200 J		200 J	
MAX REPETITION FREQUENCY	100 Hz		100 Hz		20 Hz		20 Hz	
EFFECTIVE APERTURE	65 x 65 mm		65 x 65 mm		65 x 65 mm		65 x 65 mm	
MEASUREMENT CAPABILITY								
Spectral Range *	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator
	0.19 – 20 μm	0.3 - 2.1 μm	0.19 – 20 μm	0.3 - 2.1 μm	0.19 – 20 μm	0.3 - 2.1 μm	0.19 – 20 μm	0.3 - 2.1 μm
Maximum Measurable Energy ^{a,b}	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator
1064 nm, 150 μs pulse, Single shot ^c	25 J	200 J	25 J	200 J	50 J	200 J	50 J	200 J
1064 nm, 7 ns, 10 Hz	25 J	125 J	25 J	125 J	25 J	125 J	25 J	125 J
266 nm, 7 ns, 10 Hz	20 J	35 J	20 J	35 J	20 J	35 J	20 J	35 J
Noise Equivalent Energy ^d	10 μJ		10 μJ		20 μJ		20 μJ	
Sensitivity ^{e,f}	4 V/J		4 V/J		1.5 V/J		1.5 V/J	
Max Repetition Frequency	100 Hz		100 Hz		20 Hz		20 Hz	
Maximum Pulse Width (typical)	0.7 ms		0.7 ms		5 ms		5 ms	
Rise Time (typical 0-100 %)	1 ms		1 ms		6 ms		6 ms	
Calibration Uncertainty ^g	±3 %		±3 %		±3 %		±3 %	
Repeatability	<0.5 %		<0.5 %		<0.5 %		<0.5 %	
DAMAGE THRESHOLDS								
Maximum Average Power	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator
All Wavelengths	12 W	30 W	40 W	90 W	12 W	30 W	40 W	90 W
Maximum Energy Density	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator	Alone	Attenuator
1064 nm, 150 μs, 10 Hz	1.2 J/cm ²	14 J/cm ²	1.2 J/cm ²	14 J/cm ²	1.2 J/cm ²	14 J/cm ²	1.2 J/cm ²	14 J/cm ²
1064 nm, 7 ns, single shot	0.6 J/cm ²	16 J/cm ²	0.6 J/cm ²	16 J/cm ²	0.6 J/cm ²	16 J/cm ²	0.6 J/cm ²	16 J/cm ²
1064 nm, 7 ns, 10 Hz	0.6 J/cm ²	8 J/cm ²	0.6 J/cm ²	8 J/cm ²	0.6 J/cm ²	8 J/cm ²	0.6 J/cm ²	8 J/cm ²
532 nm, 7 ns, 10 Hz	0.6 J/cm ²	6 J/cm ²	0.6 J/cm ²	6 J/cm ²	0.6 J/cm ²	6 J/cm ²	0.6 J/cm ²	6 J/cm ²
266 nm, 7 ns, 10 Hz	0.5 J/cm ²	1 J/cm ²	0.5 J/cm ²	1 J/cm ²	0.5 J/cm ²	1 J/cm ²	0.5 J/cm ²	1 J/cm ²
Maximum Average Power Density (@12 W)	10 W/cm ²	600 W/cm ²	10 W/cm ² ^h	600 W/cm ²	10 W/cm ²	600 W/cm ²	10 W/cm ² ^h	600 W/cm ²
PHYSICAL CHARACTERISTICS								
Effective Aperture (with Attenuator)	65 X 65 mm (62 X 62 mm)							
Absorber	Multi-Band		Multi-Band		Multi-Band		Multi-Band	
Dimensions	90H x 90W x 20D mm		90H x 90W x 94D mm		90H x 90W x 20D mm		90H x 90W x 94D mm	
Weight	440 g		900 g		440 g		900 g	
ORDERING INFORMATION								
	Standard	With Attenuator ⁱ	Standard	With Attenuator ⁱ	Standard	Standard		
Product Name	QE65LP-S-MB	QE65LP-S-MB-QED	QE65LP-H-MB-DO	QE65LP-H-MB-QED	QE65ELP-S-MB-DO	QE65ELP-H-MB-DO		
Product Number (without stand)	201251	202190	201253	202191	201279	201280		
Add Extension for INTEGRA (USB)	-INT	-INT	-INT	-INT	-INT	-INT		
Product Number (without stand)	202766	202768	202762	202764	202760	202758		
Add Extension for INTEGRA (RS-232)	-IDR	-IDR	-IDR	-IDR	-IDR	-IDR		
Add Extension for INTEGRA (Ext Trig)	-INE	-INE	-INE	-INE	-INE	-INE		

Specifications are subject to change without notice // Compatible stands: P/N 200428, 201284

* For the calibrated spectral range, see the user manual.

a. Not exceeding Maximum Average Power.

b. Maximum measurable energy depends on the monitor.

c. Increasing pulse width increases the maximum measurable energy.

d. Nominal value, actual value depends on electrical noise in the measurement system.

e. Load: 1 MΩ and ≤ 30 pF.

f. Maximum output voltage = sensitivity x maximum energy.

g. Excludes non-linearities.

h. At 12 W. Maximum Average Power Density is 5 W/cm² @ 40 W.

i. When -QED extension is added, the QE + QED come as one unit with a combined calibration only. See the "QED Attenuator" page for more options on the calibration.