



UP12-H

12 mm Ø, 1 mW - 110 W



KEY FEATURES

1. **MODULAR CONCEPT**
Increase the power capability of your detector: 3 different cooling modules
2. **HIGH PERFORMANCE**
Fast Rise Time (0.3 sec)
High Damage Threshold (36 kW/cm²)
3. **COMPACT DESIGN**
Only 14 mm thick (10S model)
4. **ENERGY MODE**
Measure single shot energy up to 5 J
5. **SMART INTERFACE**
Containing all the calibration data
6. **integra OPTIONS**
 - Standard: USB Output (-INT)
 - In Option: RS-232 Output (-IDR)

AVAILABLE MODELS



UP12E-10S-H5
(10W-Standalone)



UP12E-20H-H5
(20W-Heatsink)



UP12E-70W-H5
(70W-Water-Cooled)

ACCESSORIES



Stand with Steel Post
(Model Number: 200160)



Extension Cables
(4, 15, 20 or 25 m)



Fiber Adaptors and Connectors
(FC, SC or SMA)



Pelican Carrying Case

SEE ALSO

HOW IT WORKS	14
CALIBRATION	6
TECHNICAL DRAWINGS	96
ABSORPTION CURVES	100
OEM DETECTORS	148
COMPATIBLE MONITORS	
MAESTRO	20
TUNER	24
UNO	26
S-LINK	28
P-LINK	30
M-LINK	32
LIST OF ALL ACCESSORIES	194
APPLICATION NOTE	
MEASURING LASER POWER WITH A THERMOPILE DETECTOR: THE BASICS!	202175

UP12-H



*Also traceable to NRC-CNRC

SPECIFICATIONS

	UP12E-10S-H5	UP12E-20H-H5	UP12E-70W-H5
MAX AVERAGE POWER (CONTINUOUS / 1 MINUTE)	10 W / 20 W	20 W / 40 W	70 W [†] / 110 W [†]
EFFECTIVE APERTURE	12 mm Ø	12 mm Ø	12 mm Ø
COOLING METHOD	Convection	Heatsink	Water-Cooled
MEASUREMENT CAPABILITY			
Spectral Range *	0.19 – 20 µm	0.19 – 20 µm	0.19 – 20 µm
Noise Equivalent Power ^a	1 mW	1 mW	1 mW
Rise Time (nominal) ^b	0.3 sec	0.3 sec	0.3 sec
Sensitivity (typ into 100 kΩ load) ^c	0.53 mV/W	0.53 mV/W	0.53 mV/W
Calibration Uncertainty ^d	±2.5 %	±2.5 %	±2.5 %
Repeatability	±0.5 %	±0.5 %	±0.5 %
Energy Mode			
Sensitivity	0.84 mV/J	0.84 mV/J	0.84 mV/J
Maximum Measurable Energy ^e	5 J	5 J	5 J
Noise Equivalent Energy ^a	0.02 J	0.02 J	0.02 J
Minimum Repetition Period	1.5 sec	1.5 sec	1.5 sec
Maximum Pulse Width	50 ms	50 ms	50 ms
Accuracy with energy calibration option	±5 %	±5 %	±5 %
DAMAGE THRESHOLDS			
Maximum Average Power Density ^g	36 kW/cm ²	36 kW/cm ²	36 kW/cm ²
Pulsed Laser Damage Thresholds	Max Energy Density		Peak Power Density
1064 nm, 360 µs, 5 Hz	5 J/cm ²		14 kW/cm ²
1064 nm, 7 ns, 10 Hz	1 J/cm ²		143 MW/cm ²
532 nm, 7 ns, 10 Hz	0.6 J/cm ²		86 MW/cm ²
266 nm, 7 ns, 10 Hz	0.3 J/cm ²		43 MW/cm ²
PHYSICAL CHARACTERISTICS			
Effective Aperture	12 mm Ø	12 mm Ø	12 mm Ø
Absorber (High Damage Threshold)	H5	H5	H5
Dimensions	38H x 38W x 14D mm	38H x 38W x 45D mm	38H x 38W x 32D mm
Weight (head only)	0.13 kg	0.15 kg	0.19 kg
ORDERING INFORMATION			
Product Name	UP12E-10S-H5-D0	UP12E-20H-H5-D0	UP12E-70W-H5-D0
Product Number (without stand)	200383	200385	200389
Add Extension for INTEGRA (USB)	-INT	-INT	-INT
Product Number (without stand)	202613	202615	203037
Add Extension for INTEGRA (RS-232)	-IDR	-IDR	-IDR

Specifications are subject to change without notice // Compatible stand: P/N 200160

* For the calibrated spectral range, see the user manual.

- a. Nominal value, actual value depends on electrical noise in the measurement system.
 b. With anticipation.
 c. Maximum output voltage = sensitivity x maximum power.
 d. Including linearity with power.
 e. For 360 µs pulses. Higher pulse energy possible when customized for long pulses (ms), less for short pulses (ns).
 f. Minimum cooling flow 0.5 liters/min, water temperature ≤ 22°C, 1/8 NPT compression fittings for 1/4 inch semi-rigid tube. Contact Gentec-EO for clean deionized water cooling module option.
 g. At 1064 nm, 10 W CW.

PHOTO TECHNICA フォトテクニカ株式会社 〒336-0017 埼玉県さいたま市南区南浦和 1-2-17 <http://www.phototechnica.co.jp>
 TEL: 048-871-0067 FAX: 048-871-0068 e-mail: voc@phototechnica.co.jp