



pulseSlicer

Often there is a need for a variable bandwidth or pulse width of an ultrashort laser pulse, however standard laser sources typically generate fixed or slightly variable pulses only. The *pulseSlicer* is a simple solution for narrowing broadband laser pulses by spectral cutting.

An optical system disperses the pulses spatially, and in the plane where the spectral components are separated, the spectrum is controlled via a mask. Afterwards, the dispersed pulse is recollimated.

With the narrowing of the spectrum the pulse width is modified accordingly, resulting in longer pulses. Of course the transmitted power is reduced proportionally to the amount of spectral cutting, but many applications are not power limited when considering the available laser input power.

- Easily variable output bandwidth / pulse width
- Simple solution for narrowing broadband laser pulses




PHOTO
TECHNICA 株式会社
〒336-0017 埼玉県
TEL:048-871-0000
e-mail:voc@phototech.co.jp


Specifications

Wavelength ranges	700 ... 1100 nm or 1000 ... 1600 nm (others on request)
Minimum output bandwidth $d\lambda_{out}$	0.3 nm
Static transmission T_s	0.5 ... 0.7 (depending on wavelength range)
Overall throughput	$T_s * d\lambda_{out} / d\lambda_{in}$

Option

- Autotracker - for automatic optimization to input wavelength variations

Dimensions (in mm)



Contact:
A-P-E Angewandte Physik & Elektronik GmbH
Plauener Str. 163-165 | Haus N | 13053 Berlin | Germany
T: +49 30 986 011-30 | E: sales@ape-berlin.de | www.ape-berlin.com
or
A-P-E America (for the Americas)
45401 Research Avenue | Suite 141 | Fremont, CA 94539 | USA
T: +1 (888) 690 3250 | E: sales@ape-america.com | www.ape-america.com

**PHOTO
TECHNICA** www.phototechnica.co.jp
フォトテクニカ株式会社
〒336-0017 埼玉県さいたま市南区南浦和 1-2-17
TEL:048-871-0067 FAX:048-871-0068
e-mail:voc@phototechnica.co.jp

A-P-E follows a policy of continued product improvement.
Therefore, specifications are subject to change without notice.
© A-P-E GmbH | January 2015