



# UP50-W

50 mm Ø, 5 mW – 85 W, 100 kW/cm<sup>2</sup>



## KEY FEATURES

- 1. **MODULAR CONCEPT**  
Increase the power capability of your detector:  
4 different cooling modules
- 2. **VERY HIGH DAMAGE THRESHOLD**  
100 kW/cm<sup>2</sup> in average power density
- 3. **VERY LARGE APERTURE**  
50 mm Ø effective aperture, perfect for the largest beams
- 4. **HIGHEST ENERGY READINGS IN THE SERIES**  
Measure single shot energy up to 500 J
- 5. **SMART INTERFACE**  
Containing all the calibration data
- 6. **integra OPTIONS**
  - Standard: USB Output (-INT)
  - In Option: RS-232 Output (-IDR)

## AVAILABLE MODELS



UP50N-40S-W9  
(40W-Standalone)



UP50N-50H-W9  
(50W-Heatsink)



UP50N-50F-W9  
(50W-Fan-Cooled)



UP50M-50W-W9  
(50W-Water-Cooled)

## ACCESSORIES



Stand with Steel Post  
(Model Number: 200234)



Extension Cables  
(4, 15, 20 or 25 m)



Fiber Adaptors and Connectors  
(FC, SC or SMA)



3-Port Fiber Cylinder with  
Adaptors and Plug



12V Power Supply  
(Model Number: 200130)



Pelican Carrying Case



## SEE ALSO

HOW IT WORKS	14
CALIBRATION	6
TECHNICAL DRAWINGS	92
ABSORPTION CURVES	96
OEM DETECTORS	146
COMPATIBLE MONITORS	
MAESTRO	20
TUNER	24
UNO	26
S-LINK	28
P-LINK	30
M-LINK	32
LIST OF ALL ACCESSORIES	196
APPLICATION NOTE	
MEASURING LASER POWER WITH A THERMOPILE DETECTOR: THE BASICS!	202175
MEASURING HIGH POWER WITH A LOW POWER DETECTOR	202188

## UP50-W

CE NIST\*  
Traceable  
\*Also traceable to NRC-CNRC

## SPECIFICATIONS

	UP50N-40S-W9	UP50N-50H-W9	UP50N-50F-W9	UP50M-50W-W9
MAX AVERAGE POWER (CONTINUOUS / 1 MINUTE)	40 W / 80 W	50 W / 85 W	50 W / 85 W	50 W <sup>†</sup> / 85 W <sup>†</sup>
EFFECTIVE APERTURE	50 mm Ø	50 mm Ø	50 mm Ø	50 mm Ø
COOLING METHOD	Convection	Heatsink	Fan-Cooled	Water-Cooled
MEASUREMENT CAPABILITY				
Spectral Range *	0.19 – 10.0 µm	0.19 – 10.0 µm	0.19 – 10.0 µm	0.19 – 10.0 µm
Noise Equivalent Power <sup>a</sup>	5 mW	5 mW	5 mW	5 mW
Rise Time (nominal) <sup>b</sup>	3.5 sec	3.5 sec	3.5 sec	3.5 sec
Sensitivity (typ into 100 kΩ load) <sup>c</sup>	0.12 mV/W	0.12 mV/W	0.12 mV/W	0.12 mV/W
Calibration Uncertainty <sup>d</sup>	±2.5 %	±2.5 %	±2.5 %	±2.5 %
Repeatability	±0.5 %	±0.5 %	±0.5 %	±0.5 %
Energy Mode				
Sensitivity	0.02 mV/J	0.02 mV/J	0.02 mV/J	0.02 mV/J
Maximum Measurable Energy <sup>e</sup>	500 J	500 J	500 J	500 J
Noise Equivalent Energy <sup>a</sup>	0.25 J	0.25 J	0.25 J	0.25 J
Minimum Repetition Period	11.1 sec	11.1 sec	11.1 sec	11.1 sec
Maximum Pulse Width	467 ms	467 ms	467 ms	467 ms
Accuracy with energy calibration option	±5 %	±5 %	±5 %	±5 %
DAMAGE THRESHOLDS				
Maximum Average Power Density <sup>g</sup>	100 kW/cm²	100 kW/cm²	100 kW/cm²	100 kW/cm²
Pulsed Laser Damage Thresholds	Max Energy Density		Peak Power Density	
1064 nm, 150 µs, 5 Hz	100 J/cm²		667 kW/cm²	
1064 nm, 7 ns, 10 Hz	1.1 J/cm²		157 MW/cm²	
532 nm, 7 ns, 10 Hz	1.1 J/cm²		157 MW/cm²	
248 nm, 26 ns, 10 Hz	0.7 J/cm²		27 MW/cm²	
PHYSICAL CHARACTERISTICS				
Effective Aperture	50 mm Ø	50 mm Ø	50 mm Ø	50 mm Ø
Absorber (High Damage Threshold)	W9	W9	W9	W9
Dimensions	89H x 89W x 32D mm	89H x 89W x 106D mm	89H x 89W x 116D mm	89H x 89W x 40D mm
Weight (head only)	0.62 g	0.93 g	1.38 g	0.81 g
ORDERING INFORMATION				
Product Name	UP50N-40S-W9	UP50N-50H-W9	UP50N-50F-W9	UP50M-50W-W9
Product Number (Including stand)	200896	200897	200898	201887
 Add Extension for INTEGRA (USB)	-INT	-INT	-INT	-INT
 Add Extension for INTEGRA (RS-232)	-IDR	-IDR	-IDR	-IDR
Specifications are subject to change without notice				

Specifications are subject to change without notice

\* For the calibrated spectral range, see the user manual.

a. Nominal value, actual value depends on electrical noise in the measurement system.

b. With anticipation.

c. Maximum output voltage = sensitivity x maximum power.

d. Including linearity with power.

e. For 360 µs pulses. Higher pulse energy possible when customized for long pulses (ms), less for short pulses (ns).

f. Minimum cooling flow 0.5 liters/min, water temperature ≤ 22°C, 1/8 NPT compression fittings for 1/4 inch semi-rigid tube.  
Contact Gentec-EO for clean deionized water cooling module option.

g. At 1064 nm, 10 W CW.



フォトテクニカ株式会社

〒336-0017 埼玉県さいたま市南区南浦和 1-2-17

TEL: 048-871-0067 FAX: 048-871-0068

http://www.phototechnica.co.jp

e-mail: voc@phototechnica.co.jp